


Silent Drawer System


Modul Box Assembly Instruction

Special Features:

- Length:270,300,350,400,450,500,550mm.
- The drawer side-board is 88mm high.
- Drawer width can be designed freely with automatic error adjustment.
- Hidden full pullout silencing sliding skid can bear 40kg and enjoys
- excellent stability and quite and smooth sliding performance.
- Quick installation and dismantle.
- Newly-designed built-in damper is free from reinstallation and ensures soft and smooth drawer movements.



Basic length	Internally usable drawer depth	Minimum installation depth of drawer	Minimum installation height
270mm	242mm	275mm	110mm
300mm	272mm	305mm	110mm
350mm	322mm	355mm	110mm
400mm	372mm	405mm	110mm
450mm	422mm	455mm	110mm
500mm	472mm	505mm	110mm
550mm	522mm	555mm	110mm
600mm	572mm	605mm	110mm




1. Guide Left/Right Length: 270mm, 300mm, 350mm, 400mm, 450mm, 500mm, 550mm, 600mm

2. Drawer Side & Decorative Cap Left/Right Length: 270mm, 300mm, 350mm, 400mm, 450mm, 500mm, 550mm, 600mm

3. Back connector Left / Right


4. Front connector Left / Right

Technology pivot: Bottom and Back Panel Measurement 18MM Density Panel



- LW: Inside Cabinet Width
- Bottom panel width=Inside Cabinet Width-75±0.5
Bottom panel length=Runner length-10MM
 - Back panel height= 68MM
Back panel width=Inside Cabinet Width-87±0.5

Runner Installation(mm)



Basic length:270/300/350/400/450/500/550

